

## Technical information VitoMat I Manual Filling Machine



The ColorMatic VitoMat filling machines allow ColorMatic pre-fill spray paint cans (already containing propellant and specific additives) to be filled with individual paints. There are three different VitoMat filling machines to choose from, each offering advantages for different needs. All machines fill both 400ml and 150ml cans.

### Application:

VitoMat I is ideal for filling small quantities.

## Quality and properties

- Robust, stable machine, suitable for filling micro and small quantities
- All-important functions clear to see and easy to read
- Portable, removable piston, which fits the cylinder
- Compatible with CleanJector
- No power supply required
- Mobile and flexible
- Very simple operation
- Suitable for filling 400ml and 150ml cans
- Suitable for filling 1K and 2K coating qualities
- Suitable for water- and solvent-based coats
- Fast colour change
- Very good value for money

## Physical and chemical data

- **Description:** Exterior: Case made of stainless high-grade steel with door, operation controls and control display, base plate and filling lever. Interior: Mobile lifting device with stop plate, cylinder as paint receptacle and intended holding device, mobile piston and adapter for filling
- **Measurements:** 32 x 25 x 75 cm
- **Capacity:** ca. 20 cans/ h (without colour change, depends on the viscosity of the paint)
- **Max. filling viscosity:** 300 s/DIN 4 mm
- **Life:** Long working life since there is almost no wear and tear

## Environment and labelling

**Environmentally compatible:** European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

**Disposal:** Please mind the residue inside the containers. Completely emptied containers can be used for recycling. If cans are not emptied, they should be disposed off as "special refuse".

*Only for DE: In order to ensure a high reuse and recycling rate, the legislator requires, in accordance with §15 - VerpackG, Paragraph 1, the return of transport, sales or outer packaging, alternatively, however, deviating agreements can also be made.*

**Labelling:** All products of European Aerosols comply with the current status of their labelling regulations. Classification and distinction takes place by the presently legal form of the **Globally Harmonized System of Classification and Labelling of Chemicals** (GHS) or rather by CLP 1272/2008/EG regulations. Our safety data sheets comply with the current form of REACH 1907/2006/EG, article 31 und appendix II,

## Using instructions

**Before use, carefully read and observe the warning texts on the label!**

- Easy filling process
- For detailed instructions, please refer to the attached manual
- For professional use only
- Wear appropriate protection goggles and gloves

## Hints concerning filling

If you use the intended base plate to bolt the VitoMat II firmly to the ground, working will be so much easier. The adjustable pedestals can be used to quickly stabilise the device.

## Disclaimer of liability

This application-technological information is given to the best of our knowledge. The notes mentioned herein are, however, non-binding and do not exempt you from own tests to see whether the products supplied by us are suitable for your special application. The use and processing is beyond our control and therefore exclusively in the responsibility of the user. European Aerosols is let off the liability, unless the liability-based incident is caused by a fault incurred to European Aerosols.

As of October 16, 2013

This release replaces all eventually earlier issued versions.

Print date: 19.04.2024

European Aerosols GmbH | Kurt-Vogelsang-Straße 6 | 74855 Haßmersheim | [info-de@european-aerosols.com](mailto:info-de@european-aerosols.com)