

## Technical information Spot Blender



DUPLI-COLOR Spot Blender is universally applicable for spot blending of clear coats and topcoats. It is specially formulated to ensure the overspray will blend into the transition zone, leaving no visible difference between the old and new paintwork. This reduces the need to polish.

Apply DUPLI-COLOR 2K Super Clear Coat, DUPLI-COLOR 2-coat clear lacquer, DUPLI-COLOR Auto-Spray or DUPLI-COLOR Auto-Color to the blended area, immediately after application.

**Application:**  
Ideal for spot repairs.

### Quality and properties

- Essential for spot coating
- Additional coating to DUPLI-COLOR Clear Coats and Auto-Sprays
- Simple time-saving processing
- Dissolves well
- Easy to polish
- Significantly reduces the need to polish
- Blends in seamlessly edge areas

### Physical and chemical data

- **Basis of binder:** Special resin
- **Colour:** transparent
- **Smell:** solvent
- **Temperature resistance:** to 90°C
- **Storage stability:**  
10 Jahre bei sachgerechter Lagerung (=10°-25°C, relative Luftfeuchte von max. 60%)
- **Size:**  
Aerosol cans, maximum nominal volume 150 ml

### Environment and labelling

**Environmentally compatible:** European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

**Disposal:** Please mind the residue inside the containers. Completely emptied containers can be used for recycling. If cans are not emptied, they should be disposed off as "special refuse".

*Only for DE: In order to ensure a high reuse and recycling rate, the legislator requires, in accordance with §15 - VerpackG, Paragraph 1, the return of transport, sales or outer packaging, alternatively, however, deviating agreements can also be made.*

**Labelling:** All products of European Aerosols comply with the current status of their labelling regulations. Classification and distinction takes place by the presently legal form of the **Globally Harmonized System of Classification and Labelling of Chemicals** (GHS) or rather by CLP 1272/2008/EG regulations. Our safety data sheets comply with the current form of REACH 1907/2006/EG, article 31 und appendix II,

### Using instructions

**Before use, carefully read and observe the warning texts on the label!**

#### Application

- Shake can.
- Test spray.
- Immediately after application of the lacquer, spray from a distance of 25 cm several thin coats into the outer zones.
- After curing the outer zone can be polished.

### Hints concerning application

For best results, we recommend the application of the DUPLI-COLOR Spot Blender approx. 10 cm inside and outside the edge areas.

### Disclaimer of liability

This application-technological information is given to the best of our knowledge. The notes mentioned herein are, however, non-binding and do not exempt you from own tests to see whether the products supplied by us are suitable for your special application. The use and processing is beyond our control and therefore exclusively in the responsibility of the user. European Aerosols is let off the liability, unless the liability-based incident is caused by a fault incurred to European Aerosols.

As of March 11, 2013

This release replaces all eventually earlier issued versions.

Print date: 23.04.2024

European Aerosols GmbH | Kurt-Vogelsang-Straße 6 | 74855 Haßmersheim | [info-de@european-aerosols.com](mailto:info-de@european-aerosols.com)